


BC477DCSM

Dimensions in mm (inches).



LCC2 (MO-041BB) Pinouts

Pin 1 – Collector 1 Pin 4 – Collector 2
Pin 2 – Base 1 Pin 5 – Emitter 2
Pin 3 – Base 2 Pin 6 – Emitter 1

Dual Bipolar PNP Devices in a hermetically sealed LCC2 Ceramic Surface Mount Package for High Reliability Applications

Dual Bipolar PNP Devices.

$$V_{CFO} = 80V$$

$$I_{c} = 0.1A$$

All Semelab hermetically sealed products can be processed in accordance with the requirements of BS, CECC and JAN, JANTX, JANTXV and JANS specifications.

| Parameter | Test Conditions | Min. | Тур. | Max. | Units |
|---------------------------|---------------------------|------|------|------|-------|
| V _{CEO} * | | | | 80 | V |
| I _{C(CONT)} | | | | 0.1 | Α |
| h _{FE} | $@ 5/2m (V_{CE} / I_{C})$ | 50 | | 220 | - |
| f _t | | | 150M | | Hz |
| P _D | | | | 0.36 | W |
| * Maximum Working Voltage | | | | | |

This is a shortform datasheet. For a full datasheet please contact sales@semelab.co.uk.

Semelab PIc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use.

Semelab plc.

Telephone +44(0)1455 556565. Fax +44(0)1455 552612.

Generated 2-Aug-02